

RATINGS 400 V - 50 Hz		
Standby	kVA	700
	kWe	560
Prime	kVA	636
	kWe	509

### Benefits & features

#### KOHLER premium quality

- Design offices using the latest technical innovations
- Modern fully certified factories
- A cutting edge laboratory
- The generating set, its components and a wide range of options have been fully developed, prototype tested, factory built, and production tested

#### KOHLER premium performances

- Optimized and certified sound levels
- Reliable power, even in extreme conditions
- Optimized fuel consumption
- Compact footprint
- Best quality of electricity, high starting and loading capacity, according to ISO8528-5
- Robust base frames and high-quality enclosures
- Protection of installations and people
- Approved in line with the most stringent standards

#### Engines

- Premium level engines, in-house or from strong partners
- High power density, small footprint
- Low temperature starting capability
- Long maintenance interval

#### Alternator

- Provide industry leading motor starting capability
- Made in Europe
- Built with a class H insulation and IP23

#### Cooling

- A compact and complete solution using a mechanically driven radiator fan
- Designed or optimized by KOHLER
- High temperature and altitude product capacity available

#### Base frame and enclosure

- High quality steel with enhanced corrosion resistance
- Highly durable QUALICOAT-certified epoxy paint
- Minimum 1000 hours of resistance to salt spray in accordance with ISO12944
- Ergonomic access to allow easy maintenance and connection of the generator
- Robust design optimized for transportation

### GENERAL SPECIFICATIONS

Engine brand	DOOSAN / HYUNDAI
Alternator commercial brand	KOHLER
Voltage (V)	400/230
Standard Control Panel	APM303
Optional control panel	APM403
Optional Control Panel	Terminal block
Optional control panel	M80
Consumption @ 100% load ESP (L/h) *	150
Consumption @ 100% load PRP (L/h) *	137
Emission level	Fuel consumption optimization
Type of Cooling	Mechanical driven fan
Performance class	G3

### GENERATOR SETS RATINGS

	Voltage	PH	Hz	Standby Rating			Prime Rating	
				kWe	kVA	Amps	kWe	kVA
D700	415/240	3	50	560	700	974	509	636
	400/230	3	50	560	700	1010	509	636
	380/220	3	50	560	700	1064	509	636
	200/115	3	50	560	700	2021	509	636
	240 TRI	3	50	560	700	1684	509	636
	230 TRI	3	50	560	700	1757	509	636

### DIMENSIONS COMPACT VERSION

Length (mm)	3620
Width (mm)	1960
Height (mm)	2122
Tank capacity (L)	600
Dry weight (kg)	3995

### DIMENSIONS SOUNDPROOFED VERSION

Type soundproofing	M240
Length (mm)	5303
Width (mm)	1900
Height (mm)	2661
Tank capacity (L)	600
Dry weight (kg)	5730
Acoustic pressure level @1m in dB(A) 50Hz (75% PRP)	90
Acoustic pressure level @7m in dB(A) 50Hz (75% PRP)	80

Reference Conditions: 25°C Air Inlet Temperature, 40°C Fuel Inlet Temperature, 100 kPa Barometric Pressure; 10.7 g/kg of dry air Humidity. Intake Restriction set to maximum allowable limit for clean filter; Exhaust Back pressure set to maximum allowable limit; Fuel density at 0.85 kg/L.

Data was taken from a single engine test according to the test methods, fuel specification and reference conditions stated above and is subjected to instrumentation and engine-to-engine variability. Test conducted with alternate test methods, instrumentation, fuel or reference conditions can yield different results. Data and specifications subject to change without notice.

### Engine

#### General

Engine brand	DOOSAN / HYUNDAI
Engine ref.	DP180LB *
Air inlet system	Turbo
Fuel	Diesel Fuel
Emission level	Fuel consumption optimization
Cylinder configuration	V
Number of cylinders	10
Displacement (l)	18.27
Bore (mm) * Stroke (mm)	128 * 142
Compression ratio	15 : 1
Speed 50Hz (RPM)	1500
Maximum stand-by power at rated RPM (kW)	612
Charge Air coolant	Air/Air
Frequency regulation, steady state (%)	+/- 0.25%
Injection Type	Direct
Governor type	Electronic
Air cleaner type, models	Dry

#### Fuel system

Maximum fuel pump flow (l/h)	540
Max head on fuel return line (m fuel)	1

#### Consumption with cooling system

Fuel consumption @ ESP Max Power (l/h)	149.50
Fuel consumption @ PRP Max Power (l/h)	136.40
Fuel consumption @ 75% of PRP Power (l/h)	103.80
Fuel consumption @ 50% of PRP Power (l/h)	71.20

#### Emissions

Emission PM (g/kW.h)	0.0690
Emission CO (g/kW.h)	0.71
Emission NOx (g/kW.h)	11.80
Emission HC (g/kW.h)	0.12

\* Engine reference may be partially modified depending on genset application, options selected by the customer and lead time required.

#### Lubrication System

Oil system capacity including filters (l)	34
Min. oil pressure (bar)	0.50
Max. oil pressure (bar)	
Oil sump capacity (l)	
Oil consumption 100% ESP 50Hz (l/h)	0.65

#### Air Intake system

Max. intake restriction (mm H2O)	220
Combustion air flow (l/s)	600

#### Exhaust system

	PRP	ESP
Exhaust gas flow (L/s)		1967
Exhaust gas temperature @ ESP (°C)		587
Heat rejection to exhaust (kW)		561
Max. exhaust back pressure (mm H2O)		600

#### Cooling system

Radiator & Engine capacity (l)	123
Fan power 50Hz (kW)	24
Fan air flow w/o restriction (m3/s)	13.80
Available restriction on air flow (mm H2O)	25
Type of coolant	Glycol-Ethylene
Radiated heat to ambient (kW)	57
Heat rejection to coolant HT (kW)	268
Coolant capacity HT, engine only (l)	21
Max coolant temperature, Shutdown (°C)	103
Thermostat begin of opening HT (°C)	71
Thermostat end of opening HT (°C)	85

---

**Alternator Specifications**


---

Alternator commercial brand	KOHLER
Kohler Alternator description	KH02954T
Number of pole	4
Number of bearing	Single Bearing
Technology	Brushless
Indication of protection	IP23
Insulation class	H
Number of wires	12
AVR Regulation	Yes
Coupling	Direct
Capacity for maintaining short circuit at 3 In for 10 s	Yes

---

**Application data**


---

Overspeed (rpm)	2250
Power factor (Cos Phi)	0.80
Voltage regulation at established rating (+/- %)	0.50
Wave form : NEMA=TIF	<40
Wave form : CEI=FHT	<2
Total Harmonic Distortion in no-load DHT (%)	2.4
Total Harmonic Distortion, on linear load DHT (%)	2.1
Recovery time (Delta U = 20% transient) (ms)	200

---

**Performance datas**


---

Continuous Nominal Rating 40°C (kVA)	680
Unbalanced load acceptance ratio (%)	8

Peak motor starting (kVA) based on x% voltage dip power factor at 0.3

**Alternator Standard Features**

- All models are brushless, rotating-field alternators
- NEMA MG1, IEEE, and ANSI standards compliance for temperature rise and motor starting
- The AVR voltage regulator provides superior short circuit capability
- Self-ventilated and dip proof construction
- Superior voltage waveform

*Note: See Alternator Data Sheets for alternator application data and ratings, efficiency curves, voltage dip with motor starting curves, and short circuit decrement curves.*

---

Reference Conditions: 25°C Air Inlet Temperature, 40°C Fuel Inlet Temperature, 100 kPa Barometric Pressure; 10.7 g/kg of dry air Humidity. Intake Restriction set to maximum allowable limit for clean filter; Exhaust Back pressure set to maximum allowable limit; Fuel density at 0.85 kg/L.

Data was taken from a single engine test according to the test methods, fuel specification and reference conditions stated above and is subjected to instrumentation and engine-to-engine variability. Test conducted with alternate test methods, instrumentation, fuel or reference conditions can yield different results. Data and specifications subject to change without notice.

### Dimensions compact version

Length (mm) * Width (mm) * Height (mm)	3620 * 1960 * 2122
Dry weight (kg)	3995
Tank capacity (L)	600



### M240 - Dimensions soundproofed version

Length (mm) * Width (mm) * Height (mm)	5303 * 1900 * 2661
Dry weight (kg)	5730
Tank capacity (L)	600
Acoustic pressure level @1m in dB(A) 50Hz (75% PRP)	90
Sound power level guaranteed (Lwa) 50Hz (75% PRP)	110
Acoustic pressure level @7m in dB(A) 50Hz (75% PRP)	80



### Dimensions DW compact version

Length (mm) * Width (mm) * Height (mm)	5367 * 1960 * 2219
Dry weight (kg)	4961
Tank capacity (L)	2175



### M240 - Dimensions DW soundproofed version


Length (mm) * Width (mm) * Height (mm)	5367 * 1960 * 2933
Dry weight (kg)	6671
Tank capacity (L)	2175
Acoustic pressure level @1m in dB(A) 50Hz (75% PRP)	90
Sound power level guaranteed (Lwa) 50Hz (75% PRP)	110
Acoustic pressure level @7m in dB(A) 50Hz (75% PRP)	80

\* dimensions and weight without options

Reference Conditions: 25°C Air Inlet Temperature, 40°C Fuel Inlet Temperature, 100 kPa Barometric Pressure; 10.7 g/kg of dry air Humidity. Intake Restriction set to maximum allowable limit for clean filter; Exhaust Back pressure set to maximum allowable limit; Fuel density at 0.85 kg/L.

Data was taken from a single engine test according to the test methods, fuel specification and reference conditions stated above and is subjected to instrumentation and engine-to-engine variability. Test conducted with alternate test methods, instrumentation, fuel or reference conditions can yield different results. Data and specifications subject to change without notice.

#### Basic terminal block



It is used as a basic terminal block for connecting a control unit. Offers the following functions:

- emergency stop button
- customer connection terminal block
- CE certified

#### M80



The M80 is a dual-function control panel. It can be used as a basic terminal block for connecting a control unit and as an instrument panel with a direct read facility, with displays giving a global view of your generating set's basic parameters. Offers the following functions:

- Engine parameters: tachometer, working hours counter, coolant temperature indicator, oil pressure indicator
- emergency stop button
- customer connection terminal block
- CE certified

#### APM303




The APM303 is a versatile unit which can be operated in manual or automatic mode. It offers the following features:

- Measurements: phase-to-neutral and phase-to-phase voltages, fuel level (In option : active power currents, effective power, power factors, Kw/h energy meter, oil pressure and coolant temperature levels)
- Supervision: Modbus RTU communication on RS485
- Reports: (In option : 2 configurable reports)
- Safety features: Overspeed, oil pressure, coolant temperatures, minimum and maximum voltage, minimum and maximum frequency (Maximum active power P<66kVA)
- Traceability: Stack of 12 stored events

For further information, please refer to the data sheet for the APM303

#### APM403



#### BASIC GENERATING SET AND POWER PLANT CONTROL

The APM403 is a versatile control unit which allows operation in manual or automatic mode

- Measurements : voltage and current
- kW/kWh/kVA power meters
- Standard specifications: Voltmeter, Frequency meter.
- Optional : Battery ammeter.
- J1939 CAN ECU engine control
- Alarms and faults: Oil pressure, Coolant temperature, Overspeed, Start-up failure, alternator min/max, Emergency stop button.
- Engine parameters: Fuel level, hour counter, battery voltage.
- Optional (standard at 24V): Oil pressure, water temperature.
- Event log/ Management of the last 300 genset events.
- Mains and genset protection
- Clock management
- USB connections, USB Host and PC,
- Communications : RS485 INTERFACE
- ModBUS protocol /SNMP
- Optional : Ethernet, GPRS, remote control, 3G, 4G,
- Websupervisor, SMS, E-mails

Reference Conditions: 25°C Air Inlet Temperature, 40°C Fuel Inlet Temperature, 100 kPa Barometric Pressure; 10.7 g/kg of dry air Humidity. Intake Restriction set to maximum allowable limit for clean filter; Exhaust Back pressure set to maximum allowable limit; Fuel density at 0.85 kg/L.

Data was taken from a single engine test according to the test methods, fuel specification and reference conditions stated above and is subjected to instrumentation and engine-to-engine variability. Test conducted with alternate test methods, instrumentation, fuel or reference conditions can yield different results. Data and specifications subject to change without notice.

## STANDARD SCOPE OF SUPPLY

All our gensets are fitted with:

- Industrial water cooled DIESEL engine
- Electric starter & charge alternator
- Standard air filter
- Schneider or ABB electric circuit breaker, adapted to the short-circuit current of the generating set
- Single bearing alternator IP 23 T° rise/ insulation to class H/H
- Welded steel base frame with 85% vibration attenuation mounts
- 4 lifting points on the chassis, lifting bar on the top included from 165 kVA ESP or optional
- highly durable QUALICOAT certified epoxy paint
- frame height optimized to allow it to be moved safely by forklift
- enclosure made of new high-quality European steel with enhanced corrosion resistance
- IP 64 locks, made from stainless materials
- enclosures and base frames tested and analyzed by the French Corrosion Institut
- 100% of tanks tested for permeability
- Personal protection ensured by protective grilles on hot and rotating parts
- Separate 9 dB(A) silencer
- Fuel tank welded inside the genset frame
- Retention bund included for gensets up to 110 kVA ESP
- Charged DC starting battery with electrolyte
- Emergency stop button on the outside
- Flexible fuel lines & lub oil drain cock
- Exhaust outlet with flexible and flanges
- User's manual (1 copy)
- Packing under plastic film

### Excluded from the supply:

- For XPRESS products, from 25 to 1500 kVA: oil and antifreeze liquid

## CODES AND STANDARDS

Engine-generators set is designed and manufactured in facilities certified to standards ISO9001:2015 & ISO14001:2015. The generator sets and its components are prototype-tested, factory built and production tested and are in compliance with the relevant standards:

- Machinery Directive 2006/42/EC of May 17th 2006
- EMC Directive 2014/30/UE
- Safety objectives set out in the Low Voltage Directive 2014/35/UE
- EN ISO 8528-13, EN 60034-1, EN 61000-6-1, EN 61000-6-2, EN 61000-6-3, EN 55011, EN 1679-1 et EN 60204-1

## POWER RATINGS DEFINITION according to ISO8528-1 (2018-02 edition) and ISO-3046-1

**Emergency Standby Power (ESP):** The standby rating is applicable to varying loads for the duration of a power outage. There is no overload capability for this rating. Average load factor per 24 hours of operation is <70%.

**Prime Power (PRP):** At varying load, the number of generator set operating hours is unlimited. A 10% overload capacity is available for one hour within 12 hour of operation. Average load factor per 24 hours of operation is <70%.

## TERMS OF USE

According to the standard, the nominal power assigned by the genset is given for 25°C Air Inlet Temperature, of a barometric pressure of 100 kPa (100 m A.S.L), and 30% relative humidity. For particular conditions in your installation, refer to the derating table.

---

Reference Conditions: 25°C Air Inlet Temperature, 40°C Fuel Inlet Temperature, 100 kPa Barometric Pressure; 10.7 g/kg of dry air Humidity. Intake Restriction set to maximum allowable limit for clean filter; Exhaust Back pressure set to maximum allowable limit; Fuel density at 0.85 kg/L.

Data was taken from a single engine test according to the test methods, fuel specification and reference conditions stated above and is subjected to instrumentation and engine-to-engine variability. Test conducted with alternate test methods, instrumentation, fuel or reference conditions can yield different results. Data and specifications subject to change without notice.